

AL series dimmers



SAL06P3

Single pole and 3-way

- Adjustable low-end dim setting improves lamp compatibility
- Separate DIM/BRIGHT slider allows lights to be returned to favorite setting
- Large ON/OFF switch makes turning lights ON and OFF easy



SUT7

Single pole and 3-way

- Adjustable low-level trim setting for increased lamp compatibility
- Preset feature allows user to return to previous light level when turning lights ON
- Integrated full-slide control for easy, precise operation
- Dual rated for 120V/AC and 277V/AC. Suitable for commercial and residential applications

Slide AL series dimmers

Features

- Preset feature allows user to return to previous light level when turning lights ON
- Adjustable low-end dimming range
- Fixed Rapid Start provides quick power burst to ensure lights start even at low preset light levels
- No de-rating required in multi-gang installations



SAL06P3-W
(PJS26W wallplate sold separately)

Slide dimmers, back & side wire



Rating W	Rating V/AC	Compatible lamp Types	Description	Color suffix	Catalog no.
300	120	Dimmable LED/CFL	Slide dimmer, single pole/3-way preset	B, BK, GY, LA, V, W	□ SAL06P3-___
600	120	INC, HAL, FLR, MLV, ELV			



See instruction sheet for de-rating information

Universal slide dimmers (Forward Phase-Cut)

Features

- Universal dimming of most common dimmable lighting loads (phase-cut)
- Device can be wired into either 3-Way location (load side or line side)
- Neutral is not required for installation of devices
- Radio frequency interference filtering is standard on all models
- Electrostatic discharge protection
- Precise color matching



SUT7
(PJS26W wallplate sold separately)

Universal slide dimmers



Rating W	Rating V/AC	Compatible lamp Types	Description	Color suffix	Catalog no.
450	120	Dimmable LED/CFL/FLR	Universal slide dimmer, single pole/3-way preset	BK, GY, LA, V, W	□ SUT7-___
600	277				
720	120	INC, HAL, MLV, ELV			
1000	277				

Color ordering information

For ordering devices, include Cat. no. followed by the color code: B (Brown), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White)

B	BK	GY	LA	V	W
(Brown)	(Black)	(Gray)	(Lt. Almond)	(Ivory)	(White)

Compliances, specifications and availability are subject to change without notice.

Title 20/24 Compliant

AL series dimmers



TAL06P2

Single pole and 3-way

- Green LED locator light glows softly when lights are OFF
- Adjustable low-end dim setting improves lamp compatibility
- Separate DIM/BRIGHT bars allows lights to be returned to favorite settings
- Fully adjustable Rapid Start ensures the right amount of power boost during start-up

Color change faceplate options



TAL06P2
(PJS1W wallplate
sold separately)

Toggle AL series dimmers

Features

- Preset feature allows user to return to previous light level when turning lights ON
- Adjustable low-end dimming range
- Fully adjustable Rapid Start setting for optimal lamp start-up at low preset light levels
- No de-rating required in multi-gang installations
- Each color kit package includes 3 colors

Toggle dimmers, back & side wire



Rating W	V/AC	Compatible lamp types	Description	Color suffix	Catalog no.
300	120	Dimmable LED/CFL	Toggle dimmer, single pole/3-way preset	C2, C4, C5	<input type="checkbox"/> TAL06P2-__
600	120	INC, HAL, FLR, MLV, ELV			
—	—	—	TAL06P2 Color change faceplate	B, BK, GY, LA, V, W	<input type="checkbox"/> TCK3-__

See instruction sheet for de-rating information

Color ordering information

For ordering devices, include Cat. no. followed by the color code: B (Brown), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White), C2 (Color Change Kit - Light Almond, White, Ivory), C4 (Color Change Kit - Black, White, Ivory), C5 (Color Change Kit - Black, White, Gray)

B (Brown)	BK (Black)	GY (Gray)	LA (Lt. Almond)	V (Ivory)	W (White)
LA	W	V	BK	W	V
C2 Color Kit (Light Almond, White, Ivory)			C4 Color Kit (Black, White, Ivory)		C5 Color Kit (Black, White, Gray)

Compliances, specifications and availability are subject to change without notice.