

Commercial Specification Grade Thermoplastic Wallplates

Mid-Size



INDUSTRIAL
COMMERCIAL
RESIDENTIAL

0-18
WALLPLATES

TESTING & CODE COMPLIANCE

- UL 514D and cUL Listed, UL File #E33216
- Meets Federal Specification WP-455
- Meets all CSA requirements, C22.2 no. 42.1, CSA file #9294 (4413-02).

MATERIAL CHARACTERISTICS

Meets flammability requirements per UL 94, V2 rated. Temperature Rating: -40°C to 70°C.

Commercial Thermoplastic Wallplates


FEATURES

- Mid-Size wallplates are .0375" (9.53mm) longer and wider on all sides than standard to cover large wallboard openings.
- Assures NEC®-required gap coverage for most wallboard-to-box openings.
- Virtually unbreakable polycarbonate construction – high structural rigidity, long-term form retention.
- Screw-Catch™ feature holds plate mounting screw captive for ease of installation.
- Superior abrasion and impact resistance.
- Color-matched mounting screws captive in 1 and 2 gang plates for faster installation – helps eliminate lost screws on the job.

Decorator


1 Gang

Color	Catalog No.
Almond	PJ26A
Brown	PJ26B
Black	PJ26BK
Blue	PJ26BL
Gray	PJ26GY
Red	PJ26RD
Ivory	PJ26V
Light Almond	PJ26LA
White	PJ26W



2 Gang

Color	Catalog No.
Almond	PJ262A
Brown	PJ262B
Black	PJ262BK
Blue	PJ262BL
Gray	PJ262GY
Orange	PJ262RN
Red	PJ262RD
Ivory	PJ262V
Light Almond	PJ262LA
White	PJ262W



3 Gang

Color	Catalog No.
Almond	PJ263A
Brown	PJ263B
Black	PJ263BK
Gray	PJ263GY
Ivory	PJ263V
Light Almond	PJ263LA
White	PJ263W

