

24 VAC, 3 A Power Adapter



Technical Specification

Electrical

Input	120 VAC, 60 Hz
Output	24 VAC ($\pm 5\%$), 3000 mA

Environmental

Operating Temperature	-10 °C to +40° F (14 °F to 104 °F)
Storage Temperature	-5 °C to +60° F (23 °F to 140 °F)
Operating Humidity	30% to 85%, Relative

Physical Properties

Weight	1645 g (3.63 lb)
Dimensions (L x W x H)	120.0 mm x 80.0 mm x 65.0 mm (4.72 in. x 3.15 in. x 2.56 in.)
Installation Mode	Plane Installation
Color	Black
Input Plug	2-pin North American Plug
Cord Lengths	Input: 1 m (3.28 ft) Output: AWG18 x 2C; 1.83 m (6.0 ft)

Certifications

Safety	CE, UL, SAA
--------	-------------

Dimensions (mm/inch)

