

ASR1201D ASR1201D-D

Slim Water-proof RFID Reader



Features

- RS485, Wiegand34/26 protocol(Default 34)
- 13.56MHz(Mifare)
- 125KHz(EM-ID)
- Red and Blue LEDs
- Watch dog function ensure device free from halting
- Water-proof(Outdoor use)
- Surface/Flush mounted installation



Technical Specification

Model	ASR1201D	ASR1201D-D
System		
Main Processor	8 Bit	
Read		
Read Format	13.56MHz	125KHz
Read Range	6-8cm (max.)	
Reading time	<0.1s	
Function		
Tamper Alarm	Yes	
Interface		
To Controller	RS485, Wiegand 34/26	
General		
LED Indicator	Yes	
Beep Tone	Buzzer	
Ingress Protection	IP65	
Power Supply	5-16V DC / 100mA/ 300mA/ 800mA	
Working Environment	-30°C+60°C	
Working Humidity	≤95%	
Dimension(W×D×H)	135*47.5*16mm	
Weight	0.18kg	

Dimensions

