

DH-PFM112



Features

- Use TLC storage medium, cost-effective;
- High transmission speed, to be a higher class UHS-I, at least to be 10MB/s;
- High adaptability, water-proof, shock-proof, X-ray proof, high and low temperature resistance, etc.
- Wide application, be applied on the scenarios which will be light storage in the consumer products, relatively low video intensity or used in the relatively simple environment.

Model	DH-PFM112
Image	@lhua 64 愛当
Product type	Dedicated TF card, Micro SD card
Nominal capacity	64GB
Property/Speed	Class 10, UHS-I(reading speed: 48MB/s, writing speed: 20MB/s)
Compatibility	Compatible with the devices which can support micro SDHC, micro SDXC, micro SDHC UHS-I and micro SDXC UHS-I, especially DAHUA IP Cameras !
Dimension(L*W*H)	15.0mmx11.0mmx1.0mm
N.W.	31.6g
Color	Red& grey
Storage temperature	-25℃~85℃
Working temperature	-15℃~70℃
Humidity	0~95%(non-condensing)
Carried standard	CE/FCC
Warranty	2 years

Specifications



DH-PFM112

Dimensions (mm)

