



Features

- Use TLC storage medium, cost-effective
- High transmission speed, at least 10MB/s
- High adaptability, water-proof, shock-proof, X-ray proof, high and low temperature resistance
- Wide surveillance applications

Specifications

Model	DH-PFM112
Product type	Dedicated TF card, Micro SD card
Nominal capacity	128 GB
Property/Speed	Class 10, UHS-I(reading speed: 48MB/s, writing speed: 20MB/s)
	Compatible with the devices which can support micro SDHC, micro
Compatibility	SDXC, micro SDHC UHS-I and micro SDXC UHS-I, especially DAHUA
	IP Cameras
Dimension(L*W*H)	15.0 mm x 11.0 mm x 1.0 mm
N.W.	31.6 g
Color	Red and Gray
Storage temperature	-25℃ to 85℃
Working temperature	-15℃ to 70℃
Humidity	0% to 95%(non-condensing)
Carried standard	CE/FCC
Warranty	2 Years



DH-PFM113

Dimensions (mm)

