

# PFS3006-4ET-60

## 4-Port Fast Ethernet PoE Switch



### Product Overview

PFS3006-4ET-60 is a 4-port fast Ethernet switch, which supports 250 meters long distance PoE transmission. It provides 4\*10/100Mbps PoE ports and 2\*100 Mbps uplink ports. The product is equipped with two transmission modes (Default/Extend), which are controlled by DIP switch.

### Features

- Layer two commercial switch
- Supports IEEE802.3, IEEE802.3u and IEEE802.3X standards
- MAC auto learning, aging, MAC address capacity is 2K
- Supports MDI/MDIX self-adaptation
- RJ45 port supports 10/100 Mbps self-adaptation
- Supports IEEE802.3af and IEEE803.3at power supply standards
- Adopts metal enclosure
- Supports Hi-PoE 60W
- Supports DC 48-57V power supply

### Technical Specification

Model	PFS3006-4ET-60
Ethernet Port	2*10/100Mbps Uplink ports 4*10/100 Mbps PoE ports
PoE Power Consumption	Port1≤60W, Port2-4≤30W, Totals≤60W
PoE Protocol	IEEE802.3af (PoE), IEEE802.3at (PoE+), Hi-PoE
Switching Capacity	1.8Gbps
Packet Forwarding Rate	890kpps
Packet Buffer Memory	768Kb
MAC Table Size	2K
Flow Control	Enable by default
Application Humidity	10%~90%
Power	DC48~57V power adapter
Lightning Protection	Common Mode 2KV Differential Mode 0.5KV
Working Temperature	-10°C~+55°C
Weight	0.3kg
Dimension(W×D×H)	130mm×85mm×26mm