

Speakers blend in. Your music stands out.

IJ

Introducing the JBL B-Series in-ceiling loudspeakers. Designed with paintable grilles to blend into your décor and crafted for wide sound dispersion, the JBL B-Series loudspeakers feature a modern, virtually invisible design, powerful JBL Signature sound and are easy to install. Built to last with quality materials including a moisture-resistant design, which are perfect for bathroom installations, the JBL B-Series loudspeakers also deliver high power handling and sensitivity for full sound.

Features

- ► Powerful JBL sound quality
- ► Easy installation
- ► Zero bezel grille
- Wide sound dispersion

B-SERIES LOUDSPEAKER

In-ceiling and in-wall loudspeakers



Features and Benefits

Powerful JBL sound quality

Immerse yourself in an amazing room-filling audio experience.

Easy installation

The standard 'dog-leg' brackets save installation time and provide a sturdy, reliable fit.

Zero bezel grille

Seamlessly blending them into the room ceiling and wall.

Wide sound dispersion

Experience room filling audio regardless of what angle the speakers are installed.

What's in the box:

Main Unit Grille Owner's Manual Wall cut-out template Warranty Card

Technical Specifications: B-6IC 6.5" In-Ceiling

- Nominal Impedance: A obn
- Power (RMS/Peak): 35/140W
- Frequency Response: 50Hz 20kHz
- Loudspeaker Sensitivity: 90dB
- Woofer: 6.5" (165mm) Poly woofer
- Twootor: 0.5" (12mm) Polymor Twooto
- Cutout Dimonsione: 7 0" (202mm)
- Grille Finished Dimensions: 9.1" (232mm)
- ► Mounting Depth: 3.6" (92mm)

B-8IC

- 8" In-Ceiling
- Nominal Impedance: 4 ohm
- Power (RMS/Peak): 40/160W
- Frequency Response: 45Hz 20KHz
- Loudspeaker Sensitivity: 92dB
- ► Woofer: 8" (203mm) Poly woofer
- ► Tweeter: 0.5" (13mm) Polymer Tweeter
- ► Cutout Dimensions: 9.6" (243mm)
- ► Grille Finished Dimensions: 10.7" (272mm)
- Mounting Depth: 3.9" (100mm)

B-6ICDT

6.5" Stereo In-Ceiling

- ► Nominal Impedance: 4 ohm
- ► Power (RMS/Peak): 35/140W
- ► Frequency Response: 50Hz 20kHz
- ► Loudspeaker Sensitivity: 90dB
- ► Woofer: 6.5" (165mm) Poly woofer
- ► Tweeter: 0.5" (13mm) Polymer Tweeter
- ► Cutout Dimensions: 7.9" (202mm)
- ► Grille Finished Dimensions: 9.1" (232mm)
- ► Mounting Depth: 3.6" (92mm)

B-6IW 6.5" In-Wall

- Nominal Impedance: 4 ohm
- ▶ Power (RMS/Peak): 35/150W
- ► Frequency Response: 50Hz 20kHz
- Loudspeaker Sensitivity: 91dB
- ► Woofer: 6.5" (165mm) Poly woofer
- Tweeter: 0.5" (13mm) Polymer Tweeter
- Cutout Dimensions: 9.7" x 7.2" (246mm x 182mm)
- Grille Finished Dimensions: 8.4" x 10.9" (213mm x 277mm)
- ► Mounting Depth: 3.3" (84mm)

B-8IW

8" In-Wall

- ► Nominal Impedance: 4 ohm
- Power (RMS/Peak): 45/160W
- ► Frequency Response: 45Hz 20kHz
- Loudspeaker Sensitivity: 91dB
- ► Woofer: 8" (203mm) Poly woofer
- Tweeter: 0.5" (13mm) Polymer Tweeter
- Cutout Dimensions: 11.7" x 8.8" (299mm x 223mm)
- Grille Finished Dimensions: 10" x 12.9" (255mm x 329mm)
- ► Mounting Depth: 3.7" (96mm)



HARMAN International Industries, Incorporated 8500 Balboa Boulevard, Northridge, CA 91329 USA www.jbl.com © 2018 HARMAN International Industries, Incorporated. All rights reserved. JBL is a trademark of HARMAN International Industries, Incorporated, registered in the United States and/or other countries. Features, specifications and appearance are subject to change without notice.