

C-SERIES

In-ceiling and in-wall loudspeakers



Speakers blend in. Your music stands out.

Introducing the JBL C-Series in-ceiling loudspeakers. Designed with paintable grilles to blend into your décor and crafted for wide sound dispersion, the JBL C-Series loudspeakers feature a modern, virtually invisible design, powerful JBL Signature sound and are easy to install. Built to last with quality materials including a moisture-resistant design, which are perfect for bathroom installations, the JBL C-Series loudspeakers also deliver high power handling and sensitivity for full sound.

Features

- ► Powerful JBL sound quality
- ► Easy installation
- ► Paintable grille
- ► Moisture-resistan
- ► High-power handling and sensitivity
- ► Wide sound dispersion



C-SERIES

In-ceiling and in-wall loudspeakers



Features and Benefits

Powerful JBL sound quality

Immerse yourself in an amazing room-filling audio experience.

Easy installation

The standard 'dog-leg' brackets save installation time and provide a sturdy, reliable fit.

Paintable grille

The paintable grille makes the speakers virtually invisible, seamlessly blending them into the room decor.

Moisture-resistant

Built to last with high quality materials for many home applications.

High-power handling and sensitivity

Full sound without the need for a lot of power.

Wide sound dispersion

Experience room filling audio regardless of what angle the speakers are installed.

What's in the box:

Paint shield
Owner's manual
Wall cut-out template Warranty card











Feature	C-6IC	C-8IC	C-6ICDT	C-6IW	C-8IW
Nominal Impedance:	8-Ohm Compatible	8-Ohm Compatible	8-Ohm Compatible	8-Ohm Compatible	8-Ohm Compatible
Power (RMS/Peak):	35/140W	40/160W	35/140W	35/150W	45/160W
Frequency Response:	50Hz – 20kHz	45Hz – 20kHz	50Hz – 20kHz	50Hz – 20kHz	45Hz – 20kHz
Loudspeaker Sensitivity:	91dB	89dB	87dB	89dB	89dB
Woofer:	6.5" (165mm) Poly woofer	8" (203mm) Poly woofer	6.5" (165mm) Poly woofer	6.5" (165mm) Poly woofer	8" (203mm) Poly woofer
Tweeter:	0.5" (13mm) Polymer Tweeter	0.5" (13mm) Polymer Tweeter	0.5" (13mm) Polymer Tweeter	0.5" (13mm) Polymer Tweeter	0.5" (13mm) Polymer Tweeter
Cutout Dimensions:	7.7" (195mm)	9.4" (238mm)	7.7" (195mm)	7.4" x 10.8" (188.6mm x 275.1mm)	8.8" x 12.9" (223.4mm x 326.4mm)
Grille Finished Dimensions:	9" (228mm)	10.7" (271.7mm)	9" (228mm)	8.7" x 12" (220mm x 306.5mm)	10" x 14.1" (255mm x 358mm)
Mounting Depth:	2.9" (73mm)	3.3" (84mm)	2.9" (73mm)	3" (75mm)	3.2" (81mm)

