

## **Power-feed Modules EP-7631 and EP-7641 Potential Distribution Modules EP-700F, EP-710F, EP-711F, EP-751F, and EP-750F**



**Power-feed Module**

GE provides RSTi-EP power-feed modules (EP-7631 and EP-7641), which are used to refresh the current paths and isolate the power supply. The RSTi-EP station's main power supply is always fed in through the network adapter. Each module has a Module Status LED and connector block LEDs for inspection.

The power-feed module EP7631 must be connected if the current demand of the series of input modules is too large. The power-feed module EP-7641 must be connected if the current demand of the series of output modules is too large.

The potential distribution module EP-700F provides 16 connections for the functional earth.

The potential distribution module EP-711F provides 16 connections for +24 V from the input current path.

The potential distribution module EP-751F provides 16 connections for +24 V from the output current path.

The potential distribution module EP-710F provides 16 connections for ground from the input current path.

The potential distribution module EP-750F provides 16 connections for ground from the output current path.

Power-feed and potential distribution modules are passive modules without fieldbus communication, therefore they are not considered during configuration. A maximum of three passive modules (power-feed module, potential distribution module, empty slot module) may be installed in succession, however the next module to be installed must be an active module.

The RSTi-EP station is usually installed on a horizontally positioned DIN rail. Installation on vertically positioned DIN rails is also possible.

Modules should be allowed to de-energize for a minimum 10 seconds after power down, prior to starting any maintenance activity.

In the case of a maximum power supply of >8 A and a maximum temperature of > +55 °C, all four contacts must be connected with 1.5 mm<sup>2</sup> wiring

Refer to the *RSTi-EP Slice I/O User Manual* (GFK-2958) for additional information.

Refer to the *RSTi-EP Power Supply Reference Guide*, a software utility available on PME V9.00, for detailed power-feed requirements.

### **Module Features**

- Spring style technology for ease of wiring
- DIN rail mounted
- Double-click installation for positive indication of correct installation

GFK-2963A

**Ordering Information**

Module	Description
EP-7631	Power Module, 1 Channel 24VDC Input Flow 10A
EP-7641	Power Module, 1 Channel 24VDC Output Flow 10A
EP-711F	Power Module, 16 Channels 24VDC Potential Distribution +24 VDC from Input Current Path
EP-751F	Power Module, 16 Channels 24VDC Potential Distribution +24 VDC from Output Current Path
EP-700F	Power Module, 16 Channels 24VDC Potential Distribution Functional Earth
EP-710F	Power Module, 16 Channels 24VDC Potential Distribution +0VDC from Input Current Path
EP-750F	Power Module, 16 Channels 24VDC Potential Distribution +0VDC from Output Current Path

**Specifications****Power-feed Modules**

	EP-7631	EP-7641
<b>Supply</b>		
Supply voltage	20.4V – 28.8V	
Maximum feed current for input modules	10 A	--
Current consumption from output input path I <sub>IN</sub>	10 mA	--
Maximum feed current for output modules	--	10 A
Current consumption from output input path I <sub>OUT</sub>	--	10 mA
Operating temperature	-20°C to +60°C (-4 °F to +140 °F)	
Storage temperature	-40°C to +85°C (-40 °F to +185 °F)	
Air humidity (operation/transport)	5% to 95%, noncondensing as per IEC 61131-2	
<b>General Data</b>		
Width	11.5 mm (0.45 in)	
Depth	76 mm (2.99 in)	
Height	120 mm (4.72 in)	
Weight	76 g (6.21 oz)	76 g (6.21 oz)

**Power Distribution Modules**

	EP-700F	EP-711F	EP-751F	EP-710F	EP-750F
<b>Supply</b>					
Supply voltage	None	20.4V – 28.8V	20.4V – 28.8V	0 V (from input current path)	0 V (from input current path)
<b>General Data</b>					
Weight	84 g (2.96 oz)	84 g (2.96 oz)	84 g (2.96 oz)	84 g (2.96 oz)	84 g (2.96 oz)

**LEDs**

Potential distribution modules have only a Module Status LED.

**Power feed Modules**

LED	EP-7631
Module Status	Green: Voltage applied and is > 18 V DC
1.1	
1.2	
1.3	
1.4	
2.1	
2.2	
2.3	
2.4	
3.1	Green: Supply voltage for input current path > 18 V DC
3.2	Red: Supply voltage for input current path < 18 V DC
3.3	
3.4	Red: Internal fuse defective, replace module
4.1	
4.2	
4.3	
4.4	

LED	EP-7641
Module Status	Green: Voltage applied and is > 18 V DC
1.1	
1.2	
1.3	
1.4	
2.1	
2.2	
2.3	
2.4	
3.1	
3.2	
3.3	
3.4	
4.1	Green: Supply voltage for output circuit > 18 V DC
4.2	Red: Supply voltage for output circuit < 18 V DC
4.3	
4.4	Red: Internal fuse defective, replace module