24VDC LED ELECTRONIC DIMMABLE 20W CLASS 2 POWER SUPPLY ^{by} **GMLinhting**

Project:		
•		
Type:		
Location:		
Contact Phone:		

PRODUCT DESCRIPTION

Hardwire 24VDC LED dimming power supply that works with conventional low voltage electronic wall mount dimmers.


PRODUCT SPECIFICATIONS

- Output constant voltage 24VDC
- · Universal AC input/: 90-130 VAC
- · Built-in active PFC function
- · High efficiency: > 84%
- · Protections: short circuit/over loading
- Full protection plastic housing, wiring covers secured with screws
- · Easy installation
- Cooling by free air convection
- Works with leading edge and trailing edge TRIAC dimmers
- · Strong compatibility, flicker-free dimming
- · Suitable for LED lighting applications
- · Label: cETLus
- Warranty 5 years





145*55*19.5mm (L*W*H)



NOTE: Not for use with GMR4, GMR6 or SDP pucks

Catalog Number	Max. Wattage	Input Voltage	Output Voltage	Input current	output current	Weight	Dimensions		
							L	W	Н
LTHE-20-DIM-24	20W	120V/60Hz	24 VDC	0.16A	.83A MAX	.41 lbs.	5.75"	2.30"	.80 "

For voltage drop - see www.gmlighting.net/voltagedrop.html or consult GM Lighting 2015 New Product Product Brochure, page .

