

Siemens Low Voltage Residential Circuit Breakers Miniature Circuit Breakers AFCI - Combo AFCI 2-pole plug-on 10k and 22k are Circuit Protection Load Center Mains, Feeders, and Miniature Circuit Breakers. Type: Combination Type AFCI Standard: UL Listed Voltage Rating: 120/240 Amperage Rating: 15 Number Of Poles: 2 Operating Temperature: 40



Number of poles	2
Electricity	
Continuous current rated value	15 A
Supply voltage frequency rated value 50/60 Hz	Yes
Environmental conditions	
Ambient temperature during operation maximum	40 °C
Model	
Product brand name	SIEMENS
Mechanical Design	
Design of the product	Combination Type AFCI
General product approval	
Standard	UL Listed
last modified:	10/16/2018