

SL1 – IN DIFFUSION LED STRIP – INDOOR

DESCRIPTION

Diffusion LED SL-1 is a flexible 8mm linear LED strip. Available in lengths of 16 ft or 100ft rolls. It may be cut every 6 LEDs (100mm / 4"). It uses 60 LEDs per Meter (18 LEDs / ft)

FEATURES

- * 3M industrial strength adhesive tape
- * Voltage Input: 24VDC
- * Long life LED: 50,000 hours
- * Dimmable with dimming power supply
- * 24" leads on both ends of each roll

custom lengths available upon request

SPECIFICATIONS

LED: 4.8 watts/Meter (1.5 watts/ft)
LAMP LIFE: 50,000 hours LM80
POWER INPUT: 24V DC
CRI > 91

LUMENS

2700K = 394 lm/M (120 lm/ft)
3000K = 416 lm/M (126 lm/ft)
3400K = 438 lm/M (132 lm/ft)
4100K = 460 lm/M (140lm/ft)



1 BIN SELECTION
2 STEP/MACADAM ELLIPSE
3 TEST QUALITY CONTROL

ORDERING CODE

ORDERING CODE	LENGTH	VOLTAGE	COLOR
SL1-IN	16	24V	2700
SL1-IN	16 ft 100 ft	24 Volt	2700 K 3000 K 3400 K 4100 K

Project: _____
Type: _____
Date: _____
Part #: _____