

## SL3 — INDOOR DIFFUSION LED STRIP

### DESCRIPTION

Diffusion SL-3 is a flexible 8mm wide linear LED strip. It is available in 16' and 100' rolls that can be cut every 6 LEDs (50mm or 2").

### FEATURES

- \* 3M industrial strength adhesive tape
- \* Long life LED: 50,000 hrs
- \* Dimmable with dimming power supply
- \* 2' power feeds on both ends of every roll

\*CUSTOM LENGTHS AVAILABLE UPON REQUEST\*

### SPECIFICATIONS

LED: 10 W/m (3 W/ft)  
 Lamp Life: 50,000 hrs LM80  
 LED/Meter: 60/m (18/ft)  
 Power Input: 24V DC  
 CRI > 91



### LUMENS

2700K = 788 lm/m (236 lm/ft)  
 3000K = 832 lm/m (249 lm/ft)  
 3400K = 876 lm/m (263 lm/ft)  
 4100K = 908 lm/m (279 lm/ft)



**1** BIN SELECTION  
**2** STEP: MACADAM ELLIPSE  
**3** TEST QUALITY CONTROL

ORDERING  
CODE

LENGTH

VOLTAGE

COLOUR

SL3-IN	16	24V	2700
SL3-IN	16 ft 100 ft	24 Volt	2700 K 3000 K 3400 K 4100 K

Project: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Date: \_\_\_\_\_  
 Part #: \_\_\_\_\_