

SL3 — OUTDOOR DIFFUSION LED STRIP

DESCRIPTION

Diffusion SL-3 is a flexible 10mm wide linear LED strip. It is available in 16' and 32' rolls that can be cut every 6 LEDs (50mm or 2").

FEATURES

- * Includes endcaps and mounting clips with screws
- * Long life LED: 50,000 hrs
- * Dimmable with dimming power supply
- * 2' power feeds on both ends of every roll
- * IP65

CUSTOM LENGTHS AVAILABLE UPON REQUEST

SPECIFICATIONS

LED: 10 W/m (3 W/ft)
Lamp Life: 50,000 hrs LM80
LED/Meter: 60/m (18/ft)
Power Input: 24V DC
CRI > 91

LUMENS

2700K = 788 lm/m (236 lm/ft)
3000K = 820 lm/m (252 lm/ft)
3400K = 876 lm/m (263 lm/ft)
4100K = 908 lm/m (279 lm/ft)



1 BIN SELECTION
2 STEP-MACADAM ELLIPSE
3 TEST QUALITY CONTROL

ORDERING CODE

ORDERING CODE	LENGTH	VOLTAGE	COLOUR
SL3-OUT	16	24V	2700
SL3-OUT	16 ft 32 ft	24 Volt	2700 K 3000 K 3400 K 4100 K

Project: _____
Type: _____
Date: _____
Part #: _____