

# DIFFUSION

by **RJCROSS**  
architectural products ltd.

lighting

## SL6 — OUTDOOR DIFFUSION LED STRIP

### DESCRIPTION

Diffusion SL-6 is a flexible 12mm wide linear LED strip. It is available in 16' and 32' rolls that can be cut every 6 LEDs (100mm or 4").

### FEATURES

- \* Includes endcaps and mounting clips with screws
- \* Long life LED: 50,000 hrs
- \* Dimmable with dimming power supply
- \* 2' power feeds on both ends of every roll
- \* IP65

\*CUSTOM LENGTHS AVAILABLE UPON REQUEST\*

### SPECIFICATIONS

LED: 14.4 W/m (4.5 W/ft)  
Lamp Life: 50,000 hrs LM80  
LED/Meter: 120/m (36/ft)  
Power Input: 24V DC  
CRI > 91

### LUMENS

2700K = 1220 lm/m (366 lm/ft)  
3000K = 1282 lm/m (384 lm/ft)  
3400K = 1344 lm/m (402 lm/ft)  
4100K = 1400 lm/m (420 lm/ft)



ORDERING  
CODE

LENGTH

VOLTAGE

COLOUR

|         |                |         |                                      |
|---------|----------------|---------|--------------------------------------|
| SL6-OUT | 16             | 24V     | 2700                                 |
| SL6-OUT | 16 ft<br>32 ft | 24 Volt | 2700 K<br>3000 K<br>3400 K<br>4100 K |

Project: \_\_\_\_\_  
Type: \_\_\_\_\_  
Date: \_\_\_\_\_  
Part #: \_\_\_\_\_