

CUTTERS

Mini Tube Cutter



88910

For 1/8" to 5/8" (3mm – 16 mm) copper and aluminum tubing. Requires only 1-3/8" (35mm) swing radius. Not designed for cutting stainless steel or hard tempered tubing.

PVC & Multilayer Tubing Cutter



88912

Cuts 1" (25mm) O.D. multilayer plastic tubing and up to 3/4" (19 mm) schedule 40 PVC pipe.

Professional Tube Cutter



88904

Accurate 4-roller system; no spiraling. Professional reaming tool for stainless steel tubing. Extra cutting wheel included in the handle.

Ratcheting PVC Cutter



50034

Ratchet action allows easy, one-hand cutting. Quick one-handed blade release –no tools required. Cuts up to 2" PVC.

8 Piece Bi-Metal Hole Saw Kit

- Optimized teeth pattern for fast, consistent cutting of steel (including stainless steel)
- Contains the most popular sizes and two arbors in a rust proof, molded plastic carrying case
- Includes most popular sizes 7/8", 1-1/8", 1-3/8", 1-3/4", 2", and 2-1/2" hole saws



31902

HVAC Nylon Tie Tensioning Tool



86570

Excellent for securing fiberglass duct work with nylon ties; also used to secure cables and hoses.

NOTE: Read and follow safety instructions in power tool owner's manual.

Cat. No.	UPC 0-92644+	Description
86570	86570-1	HVAC Nylon Tie Tensioning Tool
88910	69077-8	Mini Tube Cutter
88912	69078-5	PVC & Multilayer Tubing Cutter
88904	88904-2	Professional Tube Cutter
50034	50034-3	Ratcheting PVC Cutter
31902	31902-0	8 pc. Hole Saw Kit
32905	69113-3	3 pc. Hole Saw Kit with Arbor (not shown)

