

M18 1 SYSTEM. 150+ TOOLS.



M18 FUEL

7" / 9" LARGE ANGLE GRINDER

7" / 9" Large Angle Grinder

2785-21 HD (0269240)

with (2) HD12.0 Batteries

2785-22 HD (0269241)

GENERATES
15A
CORDED
POWER

UP TO
2 LBS
LIGHTER

9"
GRINDING
CAPACITY

- Industry's first 18V cordless large angle grinder
- Delivers 15A power
- Replaces corded large angle grinders
- Capability to remove more material in a single pass



M18 FUEL

SUPER SAWZALL® RECIPROCATING SAW

SUPER SAWZALL®
Reciprocating
Saw Kit

2722-21 HD (0269242)

GENERATES
15A
CORDED
POWER

FASTER
THAN 15A
CORDED

UP TO
150 CUTS
PER CHARGE

- Cuts faster than 15A corded reciprocating saws and up to 40% faster than high-voltage reciprocating saws
- On/off orbital action
- 1 -1/4" Stroke length

M18 FUEL

8-1/4" TABLE SAW W/
ONE-KEY™

8-1/4" TABLE SAW W/ ONE-KEY™
2736-21 HD (0269238)
MILWAUKEE®
Folding Table Saw
Stand
48-08-0561 (0269239)



15A
CORDED
POWER

24 1/2"
RIP
CAPACITY

RIP UP TO
600 FT
PER CHARGE

M18 FUEL

18" CHAINSAW



18" CHAINSAW
2727-21 HD (0269243)

POWER
TO CUT
HARDWOODS

FASTER
THAN
GAS

UP TO
150 CUTS
PER CHARGE

M18 FUEL

7 1/4" CIRCULAR SAW



7 1/4" CIRCULAR SAW
2732-21 HD (0269237)

15A
CORDED
POWER

FASTER
THAN 15A
CORDED

UP TO
750 CUTS
PER CHARGE

HIGH OUTPUT™ HD12.0

REDLITHIUM™



50%
MORE POWER
& RUNS COOLER

VS REDLITHIUM™ HD™

FITS ALL
M18™ TOOLS

M18™ REDLITHIUM™ HIGH OUTPUT™ BATTERY



M18™ REDLITHIUM™ HIGH OUTPUT™ HD12.0 Battery Pack
48-11-1812 (0269244)

M18™ REDLITHIUM™ HIGH OUTPUT™ HD12.0 Starter Pack
48-59-1200 (0269245)



M18™ REDLITHIUM™ HIGH OUTPUT™ XC6.0 Battery Pack
48-11-1865 (0269246)

M18™ REDLITHIUM™ HIGH OUTPUT™ XC6.0 2 Pack
48-11-1862 (0269247)