

Video



Composite Video Connector

Premium gold plated RCA. Converts composite video signal from RCA to CAT-5 cable. Sold in pairs.

Works up to 2200 feet

7103-121876: MOD-VB

Shipping Weight 2 oz (.05g)



Active Component Video Balun Kit

Send component video over CAT-5 up to 500 feet point-to-point. Includes the HDTX, HDRX and 12VDC 200mA power supply.

Not for sale in countries with CE requirements

9590-526220: VBHD Kit

Shipping Weight 1.25 lbs. (.68 kg)



Active Composite Audio-Video Balun Kit

Send composite video and audio over CAT-5 up to 1000 feet point to point. Includes the CTX, CRX and 12VDC 200mA power supply.

Not for sale in countries with CE requirements

9590-526237: VBC Kit

Shipping Weight 1.25 lbs. (.68 kg)



HD Video Matrix for RNET: 4 Zone Systems

Free Video Matrix Configuration Software

Now Available

Russound's new VM1 Configuration Tool allows for the custom assignment of Video Matrix inputs and outputs to specific Russound controller amplifier sources and zones.

For a copy of the VM1 Configuration Tool software, instructions and the latest VM1 Video Matrix firmware, please visit Russound's Document Center online at www.russound.com/doccenter/doccenter.php



Video Matrix 4 zone kit

Four source, four zone high-definition Video Matrix system. RNET and RS-232 control capable. Includes: (1) 4x4 matrix (VM1), (1) power supply (A-PS) and 4 video receivers (VMR1)

EU & UK include Wall plates.



2210-527043: VM1-4

2210-527494: VM1-4 EU

2210-527500: VM1-4 UK

Shipping Weight 25 lbs. (11.3 kg)



Video Matrix 4 zone kit with 2 zone up-conversion

Four source, four zone high-definition Video Matrix system. S-video, NTSC or PAL composite video Up-conversion on two sources. RNET and RS-232 control capable. Includes: (1) 4x4 matrix (VM1), (1) power supply (A-PS) and (4) video receivers (VMR1)

EU & UK include Wall plates.



2210-527050: VM1-4UC

2210-527517: VM1-4UC EU

2210-527524: VM1-4UC UK

Shipping Weight 25 lbs. (11.3 kg)

HD Video Matrix for RNET: 8 Zone Systems



Video Matrix 8 zone kit

Eight source, eight zone high-definition Video Matrix system. RNET and RS-232 control capable. Includes: (1) 8x8 matrix (VM1), (1) power supply (A-PS) and (8) video receivers (VMR1)

EU & UK include Wall plates.



2210-527067: VM1-8

2210-527531: VM1-8 EU

2210-527548: VM1-8 UK

Shipping Weight 25 lbs. (11.3 kg)



Video Matrix 8 zone kit with 2 zone up-conversion

Eight source, eight zone high-definition Video Matrix system. S-video, NTSC or PAL composite video Up-conversion on two sources. RNET and RS-232 control capable. Includes: (1) 8x8 matrix (VM1), (1) power supply (APS) and (8) video receivers (VMR1)

EU & UK include Wall plates.



2210-527074: VM1-8UC

2210-527555: VM1-8UC EU

2210-527562: VM1-8UC UK

Shipping Weight 25 lbs. (11.3 kg)



Video Matrix 8 zone kit with 4 zone up-conversion

Eight source, eight zone high-definition Video Matrix system. S-video, NTSC or PAL composite video Up-conversion on four sources. RNET and RS-232 control capable. Includes: (1) 8x8 matrix (VM1), (1) power supply (APS) and (8) video receivers (VMR1)

EU & UK include Wall plates.



2210-527081: VM1-8UC2

2210-527579: VM1-8UC2 EU

2210-527586: VM1-8UC2 UK

Shipping Weight 25 lbs. (11.3 kg)