

A new standard in outdoor entertainment



AW4-LS-BR

4" Landscape Satellite Speaker

- Designed for excellent sonic performance in any outdoor space
- Rust-proof aluminum grille and color-molded composite construction won't chip, peel, or fade over time
- 120° vertical directional adjustment allows sound to be directed where desired in any installation
- ASA-based material design for maximum UV protection and environmental endurance from -15°F to 160°F (-25°C to 70°C)
- 70v/100v/8Ω Design for use in any application
- Includes 11" mounting stake and waterproof wire nuts
- Works with 1/2"-threaded landscape lighting mounts
- 5-year limited warranty



AW10-LSUB-BR

10" Landscape Subwoofer

- Rugged below-ground subwoofer provides superior bass while seamlessly blending into the landscape environment
- Tuned port tube that offers deep, powerful, & tight bass
- Silicone elbow for extra flexibility in any temperature extremes
- Full bandpass design
- PVC Bass Chamber for long-term durability in an underground environment
- 70v/100v/8Ω Design for use in any application
- 3-foot cable for easy connections with included weatherproof wire nuts
- 5-year limited warranty