

## A-BUS Remote Input, Single-Source Kits



### Remote Source, Single-Source/Two-Zone Kit with Remote Control

- (1) A-H1 Audio Interface Hub
- (1) A-H4P Surface Mount Hub
- (2) A-K3 Amplified Keypads
- (1) A-LRC2 Learning Remote
- (1) 1584.1 Dual IR Emitter
- (1) A-PS Power Supply
- (1) Punchdown Tool

**2000-527807: A-R320**  
 2000-530029: A-R320-EU  
 2000-530036: A-R320-UK  
 Shipping Weight 5 lbs

\*EU/UK kits contain screwless wallplates.

**CALL FOR PRICING**



### Remote Source, Single-Source/Four-Zone Kit with Remote Control

- (1) A-H1 Audio Interface Hub
- (1) A-H4P Surface Mount Hub
- (4) A-K3 Amplified Keypads
- (1) A-LRC2 Learning Remote
- (1) 1584.1 Dual IR Emitter
- (1) A-PS Power Supply
- (1) Punchdown Tool

**2000-527814: A-R340**  
 2000-530043: A-R340-EU  
 2000-530050: A-R340-UK  
 Shipping Weight 6 lbs

\*EU/UK kits contain screwless wallplates.

**CALL FOR PRICING**



### Remote Source, Single-Source/Four-Zone Kit with Remote and Local Source Input

- (1) A-H1 Audio Interface Hub
- (1) A-H4P Surface Mount Hub
- (4) A-K3 Amplified Keypads
- (1) A-LRC2 Learning Remote
- (1) A-LC3 Local Source Input
- (1) 1584.1 Dual IR Emitter
- (1) A-PS Power Supply
- (1) Punchdown Tool

**2000-527821: A-R341**  
 2000-530067: A-R341-EU  
 2000-530074: A-R341-UK  
 Shipping Weight 6 lbs

\*EU/UK kits contain screwless wallplates.

**CALL FOR PRICING**



## A-BUS Multi-source Controller and Hub



### 6 Source/8 Zone multizone controller

Rack mount, 1-unit high, rear RS-232 port, (2) RJ-45 expander jacks, (6) 845.1 single emitters. IR library, learning and paging. Controller only, no keypads. Rack ears included.

**2000-527432: A-C68**

**MSRP**  
**\$1,598.00**  
**Dealer**  
**\$799.00**



### 4 Source/4 Zone Surface Mount Hub

4 Pairs of gold plated audio RCA jacks, (4) Routed IR emitter jacks, (1) Common IR Jack, (8) RJ-45 keypad connectors, (1) 12 Volt trigger output, (2) Power supply jacks. 6.5" W x 5" H x 1.5" D (165 x 127 x 38 mm)

**2000-115882: A-H484**

Shipping Weight 2.25 lbs (.5kg)



## A-BUS Single Source



### 1 Source/2 Zone Surface Mount Hub

Gold plated audio input RCA jacks, (4) IR emitter jacks, (2) RJ-45 keypad connectors, (1) Expansion input, IR confirmation LED. 6.5" W x 2" H x 1.5" D (165 x 51 x 38 mm)

**2000-115837: A-H2**

Shipping Weight 7 oz. (198 g)



### 1 Source/4 Zone Surface Mount Hub

Gold plated audio input/output RCA jacks, (4) IR emitter jacks, (4) RJ-45 keypad connectors, RJ-45 IR link input and output, IR confirmation LED. Requires A-PS power supply. 6.5" W x 3" H x 1.225" D (165 x 76 x 32 mm)

**2000-115851: A-H4**



## A-BUS Remote Source Components



### 1 Source A-BUS Audio Interface

Uses standard RJ45 jack. Supports A-BUS hubs like the A-H4P, A-H4. IR emitter outputs for source control. 6.5" W x 3" H x 1.225" D (165 x 76 x 32 mm)

**2000-121845: A-H1**

Shipping Weight 7 oz. (198 g)



### 4 Zone Hub Panel

Single input structured wiring A-BUS Audio Distribution Hub. Requires A-BUS ready source or A-H1 Audio Interface Hub. Uses 110 punchdown connectors and CAT-5 for easy hookup. Requires A-PS power supply. 6.5" W x 3" H x 1.25" D (165 x 76 x 32 mm)

**2000-121852: A-H4P**

Shipping Weight 8 oz. (226 g)



## A-BUS Decora Style Components



### In-wall, 4 Zone Single Source Hub

Fits in a standard double gang work box. Gold plated audio input and output RCA jacks, (4) IR emitter jacks, 110 punchdown terminals, 24 VDC power and 12 VDC status jacks. **Wall plates not included** 3.625" W x 4.125" H x 1.125" D (9.2 x 10.5 x 4.8 cm)

**2000-528224: White/Almond A-H4D**

**2000-117831: Bone A-H4D**  
**2000-116056: Black A-H4D**  
**2000-117855: Brown A-H4D**



### Expansion Hub

Plugs into existing A-H4D hub for 4 additional zones. Requires A-PS and A-H4D. Installation requires a three-gang work box. \*Wall plates not included with keypads.

6.5" W x 3" H x 1.225" D (165 x 76 x 32 mm)  
**2000-528231 White/Almond A-H4DX**  
**2000-117893 Bone A-H4DX**  
**2000-117909 Black A-H4DX**  
**2000-117916 Brown A-H4DX**  
 Shipping Weight 1 lbs (.5kg)

