

# Speaker Selectors

## SS Series Single Source Selectors



### 4 pr. Speaker Selector, Single Source

100W/Ch. RMS, zone label. 4  $\Omega$  stable amplifiers & receivers. Resettable circuit protection. Impedance bypass switch for use with impedance matching volume controls. 8.5" W x 1.875" H x 6.25" D (22 x 4.8 x 16 cm)

**3630-520679: SS-4.2**  
Shipping Weight  
2.75 lbs (1.2kg)



### 6 pr. Speaker Selector, Single Source

70W/Ch. RMS, zone labels. 4  $\Omega$  stable amplifiers & receivers. Resettable circuit protection. Impedance bypass switch for use with impedance matching volume controls. 11.5" W x 1.875" H x 6.25" D (29.5 x 4.8 x 16 cm)

**3630-520686: SS-6.2**  
Shipping Weight  
3.5 lbs (1.6kg)

## Autoformer-Based Speaker Selectors with Volume Control



### 2 Pair Speaker Selector

100W/Ch. RMS. Color-coded detachable 14-gauge snap connector standard configuration is 4x - Installer may change configuration to 2x or 8x. Zone identifying labels included. 8.5" W x 3" H x 6.25" D (22 x 8 x 16 cm)

**3615-604010: SDB-2.1**  
Shipping Weight  
5.5 lbs (2.5 kg)



### 4 Pair Speaker Selector

200W/Ch. RMS. Color-coded detachable 14-gauge snap connectors. Standard configuration is 4x - Installer may change configuration to 2x or 8x. Zone identifying labels included. 17" W x 3" H x 6.25" D (43.5 x 8 x 16 cm)

**3615-604027: SDB-4.1**  
Shipping Weight  
9 lbs 4.1kg)



### 6 pair Speaker Selector

150 W/Ch. RMS. Color-coded detachable 14-gauge snap connectors. Standard configuration is 8x - Installer may change configuration to 2x or 4x. Zone identifying labels included. 17" W x 3" H x 6.25" D (43.5 x 8 x 16 cm)

**3615-604034: SDB-6.1**  
Shipping Weight  
11 lbs (5 kg)

## Autoformer-Based Speaker Selectors



### 6 pair Speaker Selector/Impedance Matching

100W/Ch. RMS with subsonic filter built in. Color-coded detachable 14-gauge snap connectors. Zone identifying labels included. 17" W x 2.875" H x 8" D (43.5 x 7.5 x 20.5 cm)

**3610-603075: PRO-6 HP**  
Shipping Weight  
9.5 lbs (4.3 kg)



### 8 pair Speaker Selector/Impedance Matching,

100W/Ch. RMS with subsonic filter, built in. Color-coded detachable 14-gauge snap connectors. Zone identifying labels included. 17" W x 2.875" H x 8" D (43.5 x 7.5 x 20.5 cm)

**3610-603136: PRO-8 HP**  
Shipping Weight 10 lbs (4.5kg)



### 12 pair Speaker Selector/Impedance Matching,

100W/Ch. RMS with subsonic filter built in. Color-coded detachable 14-gauge snap connectors. Zone identifying labels included. 17" W x 2.875" H x 8" D (43.5 x 7.5 x 20.5 cm)

**3610-603037: PRO-12 HP**  
Shipping Weight 10 lbs (4.5kg)

## Miscellaneous Speaker Selectors



### In-Wall, Dual-Source Selector

Allows a single pair of speakers to be driven by either of two amplifiers or allow a single amplifier to drive either of two pair of speakers. Decora® wallplate not included. 1" W x 2.75" H x 1.75" D (25.5 x 70 x 44.5 mm)

**3699-520501: White AB-1.2**  
**3699-520532: Almond AB-1.2**  
**3699-520556: Bone AB-1.2**  
**3699-521294: Brown AB-1.2**  
**3699-521317: Black AB-1.2**  
Shipping Weight 3 oz (85 g)



### Tabletop, Dual-Source Selector

Dual-source selector switch tabletop unit, allow a single pair of speakers to be driven by either of two amplifiers or allow a single amplifier to drive either of two pair of speakers. 5.5" W x 2.875" H x 3" D (140 x 73.5 x 76.5 mm)

**3699-520525: AB-2.2**  
Shipping Weight 1.25 lbs (.57 kg)



### Automatic Source Selector

Automatic A/B speaker selector, speaker level switching, selectable delay and sensitivity. Color-coded detachable 14-gauge snap connectors. Detachable 12VDC power supply 6.25" W x 2" H x 1.55" D (159 x 51 x 39 mm)

**3699-520914: AB-3.2**  
**3699-521270: AB-3.2 EU**  
**3699-521287: AB-3.2 UK**  
Shipping Weight 1.7 lbs (.8kg)

**REINCE**