



NUVO 65-113

20 Watt LED Bulkhead Fixture



Fixture Type Outdoor Wall Light	Collection No
Style Utility	Finish White
Length 11.25"	Width 7"
Height 5.5"	Shade Description Frosted Glass
Shade Material Glass	Number of Modules 1-Module
Light Source LED	Lumen Output 1440 Lumens
Wattage 20 Watts	Lamp Type LED
Bulb Type LED Module	Bulb Base Connector
Bulb Included Yes	Replaceable Light Source No
Safety Rated cETLus - Wet	CA Prop-65 Warning
CEC California T24 Compliant	Energy Saver Yes
Energy Star Yes	UPC 045923451133
Warranty 5-Year Warranty	Voltage 100-277 Volts
Average Rated Hours 50000	UL or ETL Listed ETL Listed
Lamp Code 20W LED BULK HEAD	Kelvin Temp 3000K
CRI 90	Supplied Bulb LED Module