

S29671

22W/LED/HID/2700K/100-277V/E26 22 watt - HID Replacement; 2700K; Medium base; 100-277

Features

- High Lumen Omni-directional LED for Industrial / Commercial applications
- Replaces HID, CFL, and Incandescent
 Ballast by-pass Direct wire only 100V 277V
- UL approved for totally enclosed fixtures
 Damp location IP65 rated
- For outdoor & indoor use
- Base up, base down or horizontal operation
- Emits no UV light / Contains no mercury (Hg)
- 5 year limited warranty
- cULus listed

Additional Technical Specifications

- Power Factor >0.9
- Operating Frequency 50-60Hz
- Working Voltage AC90-305V

Minimum Compartment Size						
Length	Width	Depth				
8.5 inch	6 inch	6 inch				

Optional Accessories

- In-line surge protector 80-929
- Mog to med socket reducer (rated up to 250V) 92-406



S29671

Item Number	Product Line	UPC	Input Voltage	Watts	Operating Frequency	Incandescent Equivalent	Fluorescent Equivalent
S29671	Hi-Pro	045923296710	100 - 277	22	50/60Hz	150W	40W

HID Equivalent	Base	ANSI Base Lamp Code		Dimmable/Non- Dimmable	Finish	MOL In Inches	MOD In Inches
100W	Medium	E26	22W/LED/HID/2700K/100-277V/E26	Non-Dimmable	White	7-11/16"	2-3/4"

2680	50000	2700	Warm White	80+	300		-20C (-4F) to a maximum of +65C (+149F)		48
Package Type	CEC Status	s Rol	HS Compliant	UL or ETL Listed			UL Classification		anty
Box	Lawful for sale California		Yes		Yes		- Damp Location Rated	5 Year I	_imited



National Toll-Free: 800.43.SATCO (800.437.2826) www.satco.com Distribution Centers: New York, Florida, Texas, Washington, California, Puerto Rico Corporate Offices: 110 Heartland Blvd., Brentwood, NY 11717 800.437.2826 631.243.2022 Fax 631.243.2027



@2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051