



# S28939

60W/LED/HID/TEMP/5K/RC/120V  
 60 watt LED Hi-lumen temporary hi-bay caged lamp; 5000K;  
 Integrated cord / plug and hook; 120 volts

### Features

- Remote control operation
- Retractable handle
- IP64 Rated
- 3 ft. cord with plug
- Outlet for connecting multiple lamps



S28939

Item Number	Product Line	UPC	Input Voltage	Watts	Power Factor	Base	ANSI Base
S28939	Hi-Pro	045923289392	120	60	>0.90	Plug 3-Prong	NEMA 5-15

  

Lamp Code	Connectable Units	Dimmable/Non-Dimmable	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
60W/LED/HID/TEMP/5K/RC/120V	10 maximum	Non-Dimmable	10-3/4"	6-1/4"	6000	50000	5000

  

Color	CRI	Beam Spread Deg	Pack	Package Type	CEC Status	RoHS Compliant	UL Classification
Natural Light	85	300	4	Box	Lawful for sale in California	Yes	cULus - Listed

  

Warranty
5 Year Limited



National Toll-Free: 800.43.SATCO (800.437.2826) www.satco.com

Distribution Centers: New York, Florida, Texas, Washington, California, Puerto Rico

Corporate Offices: 110 Heartland Blvd., Brentwood, NY 11717 800.437.2826 631.243.2022 Fax 631.243.2027

