



S29830

6A19/OMNI/220/LED/27K
 6 watt; A19 LED; 2700K; Medium base; 220' beam spread; 120 volts

Features

- Solid State LED lighting
- A shaped replacement lamp
- Long life
- Dimmable
- Approved for enclosed fixtures



S29830

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape	Base
S29830	045923298301	120	6	40W	0.98	A19	Medium
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Suggested Dimmers	Finish	MOL In Inches	MOD In Inches	Initial Lumens
E26	6A19/OMNI/220/LED/27K	Dimmable	Compatible dimmers for S29830	Frosted	4-3/16"	2-3/8"	480
Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type
25000	2700	Warm White	80	220	-25C (-13F) to a maximum of +45C (+113F)	24	Box
ENERGY STAR	CEC Status	RoHS Compliant	Fixture Type	UL or ETL Listed	UL Classification	Warranty	
ENERGY STAR	Non-Compliant Possible sub: S9703	Yes	Enclosed Rated	Yes	cULus - Damp Location Rated	5 Year Limited - 10 hour use per day	



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

