



# S29750

30W/LED/HID/MB/5000K/100-277V/E26  
 30 watt - LED HID Replacement; 5000K; Medium base;  
 Adjustable beam angle; 100-277 volts

### Features

- Replaces HID, CFL, and Incandescent
- Direct wire range voltage 100-277V
- Approved for totally enclosed fixtures
- Hi bay, low bay and post top
- Light panels lock into place creating 3 separate beam angle options
- IP65 rated
- Built-in surge protection - 1KV
- 5 year limited warranty



S29750

Specification note: Power Factor >0.9; Operating temperature range -20°C to 65°C; Operating Frequency 50-60Hz; Working Voltage AC 90-305V

Optional accessory: In-line surge protector [80-929](#)

Width (360°)	Width (270°)	Width (180°)
3.2"	6.8"	7.7"

Minimum Compartment Size		
Length	Width	Depth
11 inch	8 inch	8 inch

Item Number	Product Line	UPC	Input Voltage	Watts	Operating Frequency	Incandescent Equivalent	Fluorescent Equivalent
S29750	Hi-Pro	045923297502	100 - 277	30	50/60Hz	200W	55W

HID Equivalent	Power Factor	Base	ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches
150W	0.90	Medium	E26	30W/LED/HID/MB/5000K/100-277V/E26	Non-Dimmable	White	6-3/8"

MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature
---------------	----------------	---------------------	-------------	-------	-----	-----------------	-----------------------

3-3/16" (Open 7-11/16")	3900	50000	5000	Natural Light	80+	Adjustable: 360; 270; 180	-20C (-4F) to a maximum of +65C (+149F)
Pack	Package Type	CEC Status	RoHS Compliant	Fixture Type	UL Classification	Warranty	
24/6	Box	Lawful for sale in California	Yes	Enclosed Rated	cULus - Damp Location Rated	<a href="#">5 Year Limited</a>	



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

