



# S29676

100W/LED/HID/4000K/100-277V/EX39  
 100 watt - LED HID Replacement; 4000K; Mogul extended base; 100-277 volts

### Features

- High Lumen Omni-directional LED for Industrial / Commercial applications
- Replaces HID, CFL, and Incandescent
- Ballast by-pass - Direct wire only 100V - 277V
- UL approved for totally enclosed fixtures
- Damp location - IP65 rated
- For outdoor & indoor use
- DLC Listed
- Base up or base down operation (high/low bay and post top)
- Emits no UV light / Contains no mercury (Hg)
- Built-in surge protection - 5KV
- 5 year limited warranty
- Classified under UL 1598C
- Safety chain included

### Additional Technical Specifications

- Power Factor >0.9
- Operating temperature range -20°C to 65°C
- Operating Frequency 50-60Hz
- Working Voltage AC90-305V
- Built in surge protection

Minimum Compartment Size		
Length	Width	Depth
9.25 inch	9.25 inch	17.3 inch

Optional accessory: In-line surge protector [80-929](#)



S29676

Item Number	Product Line	UPC	Input Voltage	Watts	Operating Frequency	Incandescent Equivalent	Fluorescent Equivalent
S29676	Hi-Pro	045923296765	100 - 277	100	50/60Hz	500W	150W
HID Equivalent	Base	ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches

400W	Mogul Extended	EX39	100W/LED/HID/4000K/100- 277V/EX39		Non-Dimmable	White	9-5/8"	5.87"
Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature		Pack
13000	50000	4000	Cool White	80+	300	-20C (-4F) to a maximum of +65C (+149F)		4
Package Type	CEC Status	DLC ID:	RoHS Compliant	UL Classification	Warranty	Thermal Management		
Box	Lawful for sale in California	PLTRB8U8QX3F <a href="#">DLC Search</a>	Yes	cULus - Wet Location Rated	<a href="#">5 Year Limited</a>	<a href="#">More Details About</a>		



<p>National Toll-Free: 800.43.SATCO (800.437.2826) <a href="http://www.satco.com">www.satco.com</a></p>	<p>Distribution Centers: New York, Florida, Texas, Washington, California, Puerto Rico</p>	<p>Corporate Offices: 110 Heartland Blvd., Brentwood, NY 11717 800.437.2826 631.243.2022 Fax 631.243.2027</p>	
---	--	---	---