



S29673

45W/LED/HID/4000K/100-277V/EX39
 45 watt - LED HID Replacement; 4000K; Mogul extended base;
 100-277 volts

Features

- High Lumen Omni-directional LED for Industrial / Commercial applications
- Replaces HID, CFL, and Incandescent
- Ballast by-pass - Direct wire only 100V - 277V
- UL approved for totally enclosed fixtures
- Wet location rated
- For outdoor & indoor use
- Base up, base down or horizontal operation
- Emits no UV light / Contains no mercury (Hg)
- 5 year limited warranty
- Classified under UL 1598C

Additional Technical Specifications

- Power Factor >0.9
- Operating temperature range -20°C to 65°C
- Max Ambient Temp 65°C
- Operating Frequency 50-60Hz
- Working Voltage AC90-305V



S29673

Minimum Compartment Size		
Length	Width	Depth
17.3 inch	9.25 inch	9.25 inch

Optional accessory: In-line surge protector [80-929](#)

Item Number	Product Line	UPC	Input Voltage	Watts	Operating Frequency	Incandescent Equivalent	Fluorescent Equivalent
S29673	Hi-Pro	045923296734	100 - 277	45	50/60Hz	300W	65W

HID Equivalent	Base	ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches
175W	Mogul Extended	EX39	45W/LED/HID/4000K/100-277V/EX39	Non-Dimmable	White	10-3/4"	3.69"

Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack
5850	50000	4000	Cool White	80+	300	-20C (-4F) to a maximum of +65C (+149F)	12
Package Type	CEC Status	DLC ID:		RoHS Compliant	UL Classification	Warranty	
Box	Lawful for sale in California	PLDMHG7PNEET DLC Search		Yes	cULus - Wet Location Rated	5 Year Limited	



National Toll-Free: 800.43.SATCO (800.437.2826) www.satco.com	Distribution Centers: New York, Florida, Texas, Washington, California, Puerto Rico	Corporate Offices: 110 Heartland Blvd., Brentwood, NY 11717 800.437.2826 631.243.2022 Fax 631.243.2027	
------------------------------------------------------------------------------------------------------------------	-----------------------------------------------------------------------------------------------------	---------------------------------------------------------------------------------------------------------------------------	-------------------------------------------------------------------------------------

©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051