



# S29769

75W/LED/HID/MB/5000K/100-277V/EX39  
 75 watt - LED HID Replacement; 5000K; Mogul Extended base;  
 Adjustable beam angle; 100-277 volts

### Features

- Replaces HID, CFL, and Incandescent
- Direct wire range voltage 100-277V
- Approved for totally enclosed fixtures
- Hi bay, low bay and post top
- Light panels lock into place creating 3 separate beam angle options
- IP65 rated
- Built-in surge protection - 3KV
- 5 year limited warranty



S29769

Specification note: Power Factor >0.9; Operating temperature range -20°C to 65°C; Operating Frequency 50-60Hz; Working Voltage AC 90-305V

Optional accessory: In-line surge protector [80-929](#)

Width (360°)	Width (270°)	Width (180°)
4.2"	9.3"	10.9"

Minimum Compartment Size		
Length	Width	Depth
9.25 inch	9.25 inch	8.27 inch

Item Number	Product Line	UPC	Input Voltage	Watts	Operating Frequency	Incandescent Equivalent	Fluorescent Equivalent
S29769	Hi-Pro	045923297694	100 - 277	75	50/60Hz	750W	105W

HID Equivalent	Base	ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches
400W	Mogul Extended	EX39	75W/LED/HID/MB/5000K/100-277V/EX39	Non-Dimmable	White	8-5/8"	4-3/16" (Open 10-7/8")

Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type
----------------	---------------------	-------------	-------	-----	-----------------	------	--------------

9800	50000	5000	Natural Light	80+	Adjustable: 360; 270; 180	12	Box
CEC Status	DLC ID:	RoHS Compliant	Fixture Type	UL Classification		Warranty	
Lawful for sale in California	L4HH8JPTHBS <a href="#">DLC Search</a>	Yes	Enclosed Rated	cULus - Wet Location Rated		<a href="#">5 Year Limited</a>	



<p>National Toll-Free: 800.43.SATCO (800.437.2826) <a href="http://www.satco.com">www.satco.com</a></p>	<p>Distribution Centers: New York, Florida, Texas, Washington, California, Puerto Rico</p>	<p>Corporate Offices: 110 Heartland Blvd., Brentwood, NY 11717 800.437.2826 631.243.2022 Fax 631.243.2027</p>	
---	--	---	---