



S8708

50WLED/CDL/10/4K/100-277
 50 watt Commercial LED Downlight Retrofit; 10 inch; 4000K;
 100-277 volts

Features

- Solid State LED lighting
- External driver for simple retrofitting
- Quick connect feature for easy installation
- 100-277 range voltage circuit
- 0-10V dimming



Accessories:

[80-939](#) 10" mounting plate for commercial recessed downlights.

S8708

Item Number	UPC	Voltage	Watts	Operating Frequency	Fixture Type	Base	Lamp Code
S8708	045923087080	100-277	50	50/60Hz	Retrofit	Connector	50WLED/CDL/10/4K/100-277

Dimmable/Non-Dimmable	Suggested Dimmers	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color
0-10V Dimming Only	Compatible dimmers for S8708	9-1/4"	10-7/8"	4000	50000	4000	Cool White

CRI	Operating Temperature	ENERGY STAR	CEC Status	RoHS Compliant	UL Classification	Warranty
90	-20C (-4F) to a maximum of +45C (+113F)	ENERGY STAR	Lawful for sale in California	Yes	cULus - Wet Location Rated	5 Year Limited



National Toll-Free:
 800.43.SATCO
 (800.437.2826)
www.satco.com

Distribution Centers:
 New York, Florida, Texas,
 Washington, California,
 Puerto Rico

Corporate Offices:
 110 Heartland Blvd.,
 Brentwood, NY 11717
 800.437.2826 631.243.2022
 Fax 631.243.2027

