



S8735

20WA21/LED/HID/2700K/120V/DIM/E26
 20 watt - LED A21 Hi-Pro HID Replacement; 2700K; Medium base; 120 volts

Features

- Halogen & ceramic metal halide replacement lamp
- 70w equivalent
- Approved for enclosed fixtures



S8735

Minimum Compartment Size		
Length	Width	Depth
8.5 inch	6 inch	6 inch

Item Number	Product Line	UPC	Voltage	Watts	HID Equivalent	Lamp Shape	Base
S8735	Hi-Pro	045923087356	120	20	70W	A21	Medium

ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Suggested Dimmers	Finish	MOL In Inches	MOD In Inches	Initial Lumens
E26	20WA21/LED/HID/2700K/120V/DIM/E26	Dimmable	Compatible dimmers for S8735	Frosted	5"	2-5/8"	2350

Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Burning Position	Operating Temperature	Pack
25000	2700	Warm White	80	280	Universal	-20C (-4F) to a maximum of +45C (+113F)	24/6

Package Type	ENERGY STAR	CEC Status	RoHS Compliant	UL or ETL Listed	UL Classification	Warranty
Box	ENERGY STAR	Not for Sale in CA	Yes	Yes	cULus - Damp Location Rated	5 Year Limited



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

