



S29910

25T5/LED/46-840/DR

25 watt T5 LED; Miniature bi-pin base; 4000K; 50000 Average rated hours; 3500 lumens



Features

- Direct Replacement - for use on Electronic ballasts with no rewiring required*
- Replaces F54T5/HO linear fluorescent lamps
- High efficacy
- NSF Approved
- Integrated thermal fuse at pins
- 5 year Limited warranty

S29910

*May not be compatible with all rapid start ballasts.

Ballast required

View:

[Ballast Compatibility Chart](#)

Item Number	UPC	Watts	Fluorescent Equivalent	Lamp Shape	Base	ANSI Base	Lamp Code
S29910	045923299100	25	54W	T5	Miniature Bi-Pin	G5	25T5/LED/46-840/DR
Finish	MOL In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg
Gloss White	48"	3500	50000	4000	Cool White	82	185
Operating Temperature	Pack	CEC Status	DLC ID:	RoHS Compliant	UL or ETL Listed	UL Classification	Warranty
-20C (-4F) to a maximum of +45C (+113F)	10	Lawful for sale in California	PLYBR7TV2C9K DLC Search	Yes	Yes	cULus Classified - Damp Location Rated	5 Year Limited



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051