



S9022

10BR30/LED/3K/120V/6PK
 10 watt; BR30 LED; 100' beam spread; 3000K; Medium base;
 120 volts; Dimmable; 6-pack

Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Dimmable



S9022

Item Number	Product Line	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape
S9022	DiTTO	045923090226	120	10	65W	0.73	BR30
Base	ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Suggested Dimmers	Finish	MOL In Inches	MOD In Inches
Medium	E26	10BR30/LED/3K/120V/6PK	Dimmable	Compatible dimmers for S9022	Frosted	5-1/8"	3-3/4"
Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack
700	25000	3000	Warm White	80	100	-20C (-4F) to a maximum of +45C (+113F)	24/6
Package Type	ENERGY STAR	CEC Status	RoHS Compliant	UL or ETL Listed	UL Classification	Warranty	
Box	ENERGY STAR	Non-Compliant Possible sub: S8578	Yes	Yes	cULus - Damp Location Rated	3 Year Limited	



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

