



# S8736

20WA21/LED/HID/5000K/120V/DIM/E26  
 20 watt - LED A21 Hi-Pro HID Replacement; 5000K; Medium base; 120 volts

## Features

- Halogen & ceramic metal halide replacement lamp
- 70w equivalent
- Approved for enclosed fixtures

Minimum Compartment Size		
Length	Width	Depth
8.5 inch	6 inch	6 inch



S8736

Item Number	Product Line	UPC	Voltage	Watts	HID Equivalent	Lamp Shape	Base
S8736	Hi-Pro	045923087363	120	20	70W	A21	Medium

ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Suggested Dimmers	Finish	MOL In Inches	MOD In Inches	Initial Lumens
E26	20WA21/LED/HID/5000K/120V/DIM/E26	Dimmable	<a href="#">Compatible dimmers for S8736</a>	Frosted	5"	2-5/8"	2860

Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Burning Position	Operating Temperature	Pack
25000	5000	Natural Light	80	280	Universal	-20C (-4F) to a maximum of +45C (+113F)	24/6

Package Type	ENERGY STAR	CEC Status	RoHS Compliant	UL or ETL Listed	UL Classification	Warranty
Box	ENERGY STAR	Lawful for sale in California	Yes	Yes	cULus - Damp Location Rated	<a href="#">5 Year Limited</a>



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

