



S9227

LED 5.0W G9 450L 5000K
5 watt; T4 Repl. LED; 5000K; G9 base; 360° beam spread; 120 volts

Features

- Solid State LED lighting
- High Efficacy
- Long life
- Omnidirectional light
- Replaces halogen G9 lamps
- Non-Dimmable
- Not for use in totally enclosed fixtures
- Use in dry locations



S9227

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	Lamp Code
S9227	045923092275	120	5	40W	T4 Replacement	G9	LED 5.0W G9 450L 5000K

Dimmable/Non-Dimmable	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI
Non-Dimmable	2-3/8"	1.56"	450	15000	5000	Natural Light	80

Beam Spread Deg	Pack	Package Type	CEC Status	RoHS Compliant	UL or ETL Listed	Warranty
360	100/20	Box	Lawful for sale in California	Yes	Yes	3 Year Limited



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

