



S8738

20WA21/LED/HID/5000K/120-277V/E26
 20 watt - LED A21 Hi-Pro HID Replacement; 5000K; Medium base; 120-277 volts

Features

- Halogen & ceramic metal halide replacement lamp
- 70w equivalent
- Approved for enclosed fixtures

Minimum Compartment Size		
Length	Width	Depth
8.5 inch	6 inch	6 inch



S8738

Item Number	Product Line	UPC	Voltage	Watts	Operating Frequency	HID Equivalent	Lamp Shape
S8738	Hi-Pro	045923087387	120-277	20	50/60Hz	70W	A21
Base	ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens
Medium	E26	20WA21/LED/HID/5000K/120-277V/E26	Non-Dimmable	Frosted	5"	2-5/8"	2910
Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Burning Position	Operating Temperature	Pack
25000	5000	Natural Light	80	280	Universal	-20C (-4F) to a maximum of +45C (+113F)	24/6
Package Type	ENERGY STAR	CEC Status	RoHS Compliant	UL or ETL Listed	UL Classification	Warranty	
Box	ENERGY STAR	Lawful for sale in California	Yes	Yes	cULus - Damp Location Rated	5 Year Limited	



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

