



S8976

100W/LED/5PC/TEMP/STRING/120V
 100 watt LED High lumen industrial / commercial LED string light; 5 inter-connected lamps; 5000K; Integrated cord / plug; 120 volts



Features

- For use in industrial and commercial work areas
- 5 lamps per string
- IP65 - Water and dust proof
- Cord: 14/2 SJTW; 50 ft (15.2m) total length; 10 ft (3.05m) between lamps

S8976

| Item Number | Product Line | UPC | Input Voltage | Watts | Power Factor | Base | Lamp Code |
|-------------|--------------|--------------|---------------|-------|--------------|------------------------|-------------------------------|
| S8976 | Hi-Pro | 045923089763 | 120 | 100 | >0.90 | Plug 2-Prong Polarized | 100W/LED/5PC/TEMP/STRING/120V |

| Dimmable/Non-Dimmable | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp | Color | CRI |
|-----------------------|---------------|---------------|----------------|---------------------|-------------|---------------|-----|
| Non-Dimmable | 6-5/8" | 4-1/4" | 10000 | 50000 | 5000 | Natural Light | 85 |

| Beam Spread Deg | Pack | Package Type | CEC Status | RoHS Compliant | UL Classification | Warranty |
|-----------------|------|--------------|-------------------------------|----------------|-------------------|--------------------------------|
| 360 | 1 | Box | Lawful for sale in California | Yes | cULus - Listed | 5 Year Limited |



National Toll-Free:
 800.43.SATCO
 (800.437.2826)
www.satco.com

Distribution Centers:
 New York, Florida, Texas,
 Washington, California,
 Puerto Rico

Corporate Offices:
 110 Heartland Blvd.,
 Brentwood, NY 11717
 800.437.2826 631.243.2022
 Fax 631.243.2027

