



S9925

43T8/LED/96-850/BP/R17d
 43 watt T8 LED; 5000K; Recessed Double Contact base; 50000
 Average rated hours; 5500 Lumens



Features

- Direct wire 120-277V line voltage
- Double ended wiring
- No ballast or external driver required
- All glass tube
- Shatterproof coated
- NSF certified

S9925

Item Number	UPC	Voltage	Watts	Operating Frequency	Fluorescent Equivalent	Lamp Shape	Base
S9925	045923099250	120-277	43	50/60Hz	110W (T12)	T8	Recessed Double Contact HO/VHO

ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
R17d	43T8/LED/96-850/BP/R17d	Non-Dimmable	White	96"	1.00"	5500	50000

Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	CEC Status
5000	Cool White	82	210	-20C (-4F) to a maximum of +45C (+113F)	10	Eggcrate	Lawful for sale in California

RoHS Compliant	UL or ETL Listed	UL Classification	Warranty
Yes	Yes	cULus - Damp Location Rated	5 Year Limited



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

