



S9549

4JCD/G9/LED/5000K/120V/D
 4 watt; JCD LED; 5000K; G9 base; 120 volts

Features

- Solid State LED lighting
- High Efficacy
- Long life
- Dimmable

Silicon LED Replacements for Halogen G9 lamps.

Dimensions: Height 51 mm (2.01 in.) x Width 20 mm (0.79 in.) x Depth 15 mm (0.59 in.)



S9549

Item Number	UPC	Voltage	Watts	Base	Lamp Code	Dimmable/Non-Dimmable	Suggested Dimmers
S9549	045923095498	120	4	G9	4JCD/G9/LED/5000K/120V/D	Dimmable	Compatible dimmers for S9549

Finish	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Pack
Clear	480	25000	5000	Natural Light	80	360	200/20

Package Type	CEC Status	RoHS Compliant	UL or ETL Listed	UL Classification	Warranty
Box	Lawful for sale in California	Yes	Yes	cETLus - Damp Location Rated	3 Year Limited



National Toll-Free:
 800.43.SATCO
 (800.437.2826)
 www.satco.com

Distribution Centers:
 New York, Florida, Texas,
 Washington, California,
 Puerto Rico

Corporate Offices:
 110 Heartland Blvd.,
 Brentwood, NY 11717
 800.437.2826 631.243.2022
 Fax 631.243.2027

