

Data sheet

Commercial Art.No.: 07.417.6829.0

Cover MIN AD DB 7 Z

Protective cover for revos MINI housings with gasket (inside), metal



Technical data

General

Degree of protection (IP)	IP65
Inflammability class of insulation material acc. with UL94	Other
Housing material	Cast zinc
Surface	With powder coating
Colour	Grey
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

Model

DIN-size	3
Interlock	No
Locking mechanism	Single locking lever
Material locking lever	None
Cover attachment clamping	No
With sealing	Yes
With tether cord	No
With loop	No
With ring lug	No

Classification

ECLASS 8.1	27440208
ETIM 7.0	EC002314
ETIM 6.0	EC002314
ETIM 5.0	EC002314
ETIM 4.0	EC002314
ETIM 3.0	EC002314