

COMBINATION EMT & RIGID CONDUIT CONNECTORS *Ideal for rigid and EMT pipe.*

LB-XX-CG
(1/2" - 2")



LRL-XX-CG
(1/2" - 2")



LR-XX-CG
(1/2" - 2")



LL-XX-CG
(1/2" - 2")



C-XX-CG
(1/2" - 2")



T-XX-CG
(1/2" - 2")



XLS-LB-XX-CG
(1/2" - 2")



LB-XX-CG (Rigid & EMT)
(2-1/2", 3" & 4")



HOUSING	GASKET	COVER	SIZES	HARDWARE
Die cast aluminum with a grey powder coat paint finish.	Black neoprene rubber.	Stamped aluminum with a natural finish.	All units are available in 1/2", 3/4", 1", 1-1/4", 1-1/2" or 2". LB Series (EMT & Rigid) are also available in 2-1/2", 3", 3-1/2" & 4". Threaded for rigid conduit and a set screw for EMT.	All units come complete with screws.

ORDERING INFO example: LB-100-CG

SERIES	DESCRIPTION	CONDUIT ENTRY (xx)	FINISH
LB-XX-CG	LB Combination Conduit Body EMT (Set Screw) Rigid (Threaded)	50 = 1/2"	■ Grey
		75 = 3/4"	
LRL-XX-CG	LRL Combination Conduit Body EMT (Set Screw) Rigid (Threaded)	100 = 1"	
		125 = 1-1/4"	
LR-XX-CG	LR Combination Conduit Body EMT (Set Screw) Rigid (Threaded)	150 = 1-1/2"	
		200 = 2"	
LL-XX-CG	LL Combination Conduit Body EMT (Set Screw) Rigid (Threaded)		
C-XX-CG	C Combination Conduit Body EMT (Set Screw) Rigid (Threaded)		
T-XX-CG	T Combination Conduit Body EMT (Set Screw) Rigid (Threaded)		
XLS-LB-XX-CG	XLS-LB Combination Conduit Body EMT (Set Screw) Rigid (Threaded)		
LB-XX-CG EMT	LB EMT Conduit Body	250 = 2-1/2"	■ Grey
		300 = 3"	
LB-XX-CG Rigid	LB Rigid Conduit Body	350 = 3-1/2" ¹	
		400 = 4"	

¹ RIGID ONLY

