

VAKS100 WEATHER PROOF

The VAKS100 fixture is weather proof rated for use indoors and outdoors. Great for use in industrial applications or for residential and commercial applications where you want an industrial look. The VAKS100 is also available with a powder coat paint finish.

BOX Cast zinc with 3 plugs 1/2" npt (also available with 3/4" npt), ground screw and cork gasket.

FITTER Threaded die cast with cork gaskets.

SOCKET Porcelain, medium base, 4KV pulse rated socket with a nickle-plated screw shell and a spring-loaded centre contact.

globe, also available are clear prismatic, frosted and coloured globes. There are two types of coloured globes available. The GL glass is painted on the inside. The second type of glass is the RGL series, which has a more brilliant colour. This is achieved by having the colour added while the glass is being made. Both types of glass are available in the following colours amber, blue, green, red and white.

MAXIMUM WATTAGE 100w incandescent.

APPROVAL CSA



LAMP Not included.

FINISH Standard finish is raw. Also available with a powder coat paint finish. Some of the most common colours are black, red, white and blue. For other colours please consult factory.



