



WP - LARGE WALL PACK

Ideal for outdoor use such as warehouses, factory perimeters and loading docks .

HOUSING Two-piece, die-cast aluminum with 1/2" NPS tapped holes located on the top and both sides and back for conduit entry or for photocell. Side hinged refractor housing with a one-piece continuous rubber gasket to inhibit entrance of external contaminants. Fixture is painted with a polyester powder coat finish.

REFLECTOR Die formed anodized, stippled aluminum.

LENS Lens is a prismatic borosilicate glass. The lens is sealed with a one-piece continuous rubber gasket to inhibit entrance of external contaminants.

BALLAST All ballasts are Tri-Tap 120,277,347 volts. For 208CWI, 240CWI and 600 volt options, please consult factory. Available wattages are 250 and 400 watts High Pressure Sodium, 250 and 400 Metal Halide and Pulse Start.

LAMP All units come complete with lamp. If coated lamp is required please state type.



FINISH All units have a polyester powder coat finish. Standard colours are Architectural Bronze and White. For custom colours please consult factory.

SOCKET Mogul base 4KV pulse-rated socket with a nickel-plated screw shell and a spring-loaded centre contact.

OPTIONS Wire guard, polycarbonate shield, tamperproof hardware. full cut off visor, photocell and single and double fusing.

