

Ideal for entry and area lighting

Ideal for stairwells, entrances or outdoor walkways

## WALL LIGHT WL-LED

## CEILING LIGHT CL-LED



S  
E  
C  
U  
R  
I  
T  
Y



HOUSING	LEDS	LUMENS	DIMMING	MOUNTING	RATING
High quality, precision die cast aluminum housing.  Chip and fade resistant polyester powder coat finish.	High quality, Philips Rebel LEDs with integrated 90-130V AC input LED driver.  LEDs will produce 70% of initial lumens for a minimum of 50,000 hours	Highly efficient LEDs produce a minimum of 800 lumens	Dimmable with a standard TRIAC dimmer	Ideal mounting height is 8 - 10 feet	RATED IP65

### ORDERING INFO example: WL-LED-12W-NW-HG-PC

SERIES	DESCRIPTION	LED	VOLTS	LED Colour	FINISH	OPTIONS
WL-LED	LED Wall Mount Area Light	12W	90-130VAC	NW Natural White 4000K	<ul style="list-style-type: none"> <li><span style="display: inline-block; width: 15px; height: 15px; background-color: #cccccc; border: 1px solid #000; margin-right: 5px;"></span> HG Hammertone Grey</li> <li><span style="display: inline-block; width: 15px; height: 15px; background-color: #808080; border: 1px solid #000; margin-right: 5px;"></span> BZ Bronze</li> <li><span style="display: inline-block; width: 15px; height: 15px; background-color: #333333; border: 1px solid #000; margin-right: 5px;"></span> BLK Black</li> <li><span style="display: inline-block; width: 15px; height: 15px; background-color: #ffffff; border: 1px solid #000; margin-right: 5px;"></span> WH White</li> <li><span style="display: inline-block; width: 15px; height: 15px; border: 1px solid #000; margin-right: 5px;"></span> C Custom</li> </ul>	PC Photocell <sup>F</sup>
CL-LED	LED Ceiling Mount Light	12W	90-130VAC	NW Natural White 4000K	<ul style="list-style-type: none"> <li><span style="display: inline-block; width: 15px; height: 15px; background-color: #cccccc; border: 1px solid #000; margin-right: 5px;"></span> HG Hammertone Grey</li> <li><span style="display: inline-block; width: 15px; height: 15px; background-color: #808080; border: 1px solid #000; margin-right: 5px;"></span> BZ Bronze</li> <li><span style="display: inline-block; width: 15px; height: 15px; background-color: #333333; border: 1px solid #000; margin-right: 5px;"></span> BLK Black</li> <li><span style="display: inline-block; width: 15px; height: 15px; background-color: #ffffff; border: 1px solid #000; margin-right: 5px;"></span> WH White</li> <li><span style="display: inline-block; width: 15px; height: 15px; border: 1px solid #000; margin-right: 5px;"></span> C Custom</li> </ul>	



<sup>F</sup> FACTORY INSTALLED