

WP SMALL WALL PACK

Ideal for mounting above entry ways, loading docks and building perimeters.

HOUSING Die-cast aluminum with 1/2" NPS tapped holes located on the top and both sides of the fixture and mounting option on the back. Side hinged lens frame for ease of relamping.

REFLECTOR Die formed anodized stippled aluminum.

LENS The lens is a prismatic borosilicate glass, with a continuous rubber gasket around the glass and frame

BALLAST Ballasts are available in 50, 70, 100 and 150 watt High Pressure Sodium. They can be a dedicated 120 volts in Normal and High Power Factor or as a Tri-Tap. Some wattages are available in 208CWI and 240CWI. For Metal Halide 50, 70, 100, 150, 175 the standard ballast is a Tri-Tap. Some wattages are available in 208CWI and 240CWI.

LAMP All units come complete with lamp. If coated lamp is required please state type.

FINISH All units have a Powder coat paint finish. Standards are Architectural Bronze and White. For custom colours please consult factory.



SOCKET Medium or Mogul base 4KV pulse-rated socket with a nickle-plated screw shell and a spring-loaded centre contact.

OPTIONS Photocell, Wire Guard, Polycarbonate Shield, Full Cut Off Visor, Tamperproof Hardware, Single and double fusing and Quartz standby.

