



PVL3



PGM3

Product description:

PERIMALITER® PVL3 Applications

Use for wall mount perimeter lighting. Provides safety, security and identity illumination. Typical mounting is 12-15ft with typical spacing of 60-75ft.

PERIMALITER® PGM3/PGL Applications

Wall mount perimeter safety, security and identity applications. Units provide wide coverage and excellent uniformity. Can be spaced 4 to 6 times the mounting height with appropriate wattage.

Features & Benefits

PERIMALITER® PVL3

- Energy-saving 69w LED and HID systems up to 150w (50hz ballast available)
- One-piece polycarbonate lens, internally painted for lasting appearance. 6 to 1 spacing to mounting height ratio. Two HubbellGard® fasteners provide weathertight seal to housing. Door hinges and is removable.
- Housing is die cast aluminum for rugged mounting and heat dissipation. 1/2" feed-thru side hubs provided and top photocontrol hub for easy field installation. Standard mount is over recessed wiring boxes.
- Specular reflector, vertical lamp and refractor combine for efficient and uniform perimeter lighting. Max wattage is 150PS or 150HPS. 50HZ ballast available.
- Socket is porcelain medium base with spring-loaded center contact.

PERIMALITER® PGM3

- Available in 69w LED producing 4100 lumens at nominal 5000K with asymmetric distribution for typical mounting heights of 10-15 feet
- Cast aluminum door with borosilicate glass refractor. Bottom hinge allows door removal. Twin HubbellGard® screw closure for positive seal.
- Cast aluminum back housing provides firm mounting and heat dissipation. Mounts over recessed wiring boxes. Has two 1/2" conduit hubs for feed-thru wiring.
- Specular, anodized aluminum reflector panels for vertical lamp provide high performance. Typical spacing is 4-6 times mounting height.
- PGM3 has medium base socket to 150w. 250w units are mogul base. Top 1/2" hub can be used for field installation of PBT button photocontrols or conduit wiring from above.
- Socket is porcelain mogul base with spring-loaded center contact.
- Bronze powder paint finish is standard, other finishes available, consult factory.
- Wire guards and polycarbonate shield accessories are available for refractor protection.

Certifications

CSA
Wet listed

Viking Stock#s

HUB PVL330LU5KBZ - 69W 3500L LED Polycarbonate

HUB PGM330LU5KBZ - 69W 4100L LED Glass