

AV 110 Everywhere™

AV connections over UTP cabling

- Transmit over one or two UTP cables
- Extend AV signals 75-150 feet or HDBase-T to 328 feet
- 110 termination reduces installation time
- Utilize same cable for current and future applications

Save Time | Save Labor | Save Money | Save Space | Support the Future



HDBase-T | Component | Composite | VGA | USB | HDMI

USB 2.0 Full Speed 110 Extenders, 100ft

Description	Color	Catalog Number
Module 1-U	Black	IMU1101BK
	Electric Ivory	IMU1101EI
	Gray	IMU1101GY
	Office White	IMU1101OW
	White	IMU1101W



110 Termination 3.5mm Stereo Jack

Description	Color	Catalog Number
Stereo jack	Black	SF35110BK



VGA and 3.5mm HD AV Extender, 75ft

Description	Color	Catalog Number
Module 1.5-U	Black	IM15311015BK
	Electric Ivory	IM15311015EI
	Gray	IM15311015GY
	Office White	IM15311015OW
	White	IM15311015W



Tamper-Resistant Receptacle with 5V DC Power Output

Description	Color	Catalog Number
USB charger TR receptacle, (1) USB port 3A, 5V DC output, 15A, 125V AC decorator duplex	Black	AVPS15BK
	Ivory	AVPS15EI
	Gray	AVPS15GY
	Office White	AVPS15OW
	White	AVPS15W



HDMI HD 1080P AV Extender, 120–140ft

Description	Color	Style Line®	2-Unit Module
2-U	Black	ISFH110BK	IMH110ST2BK
	Electric Ivory	ISFH110EI	IMH110ST2EI
	Gray	ISFH110GY	IMH110ST2GY
	Office White	ISFH110OW	IMH110ST2OW
	White	ISFH110W	IMH110ST2W



HDBASE-T USB 2.0 IR and RS232, 330ft

Description	Color	Style Line®	3-Unit Module
3-U	Black	ISFHDBT3BK	IMHDBT3BK
	Electric Ivory	ISFHDBT3EI	IMHDBT3EI
	Gray	ISFHDBT3GY	IMHDBT3GY
	Office White	ISFHDBT3OW	IMHDBT3OW
	White	ISFHDBT3W	IMHDBT3W



110 Audio/Video Modules, 100ft

1.5 unit			1 unit,	
Color	RCA Component Video, Left/Right Audio	RCA Component Video, 3.5mm Audio	RCA Component Video, HD	RCA Left/Right Audio
Black	IMCAR11015BK	IMC3511015BK	IMCR1101BK	IMAR1101BK
Electric Ivory	IMCAR11015EI	IMC3511015EI	IMCR1101EI	IMAR1101EI
Gray	IMCAR11015GY	IMC3511015GY	IMCR1101GY	IMAR1101GY
Office White	IMCAR11015OW	IMC3511015OW	IMCR1101OW	IMAR1101OW
White	IMCAR11015W	IMC3511015W	IMCR1101W	IMAR1101W

