WPH/WGH SERIES POLYCARBONATE/GLASS WALLPACKS

Cat. #		Approvals
Job	Туре	



APPLICATIONS

· Perimeter lighting

SPECIFICATIONS


- WGH metal halide fixtures feature borosilicate glass refractor for nonyellowing. WPH HPS units have polycarbonate refractors for vandal resistance. Stainless steel Phillips head screw closure
- Cast aluminum housing with 1/2" conduit and photocontrol hubs. Box mounting adapter included
- 4-to-1 spacing ratio...has two mounting height forward projection
- 70 and 100 watt HPS and metal halide. Lamp included
- Medium base porcelain sockets
- · Dark bronze powder paint finish


LISTINGS

· Listed to UL1598 for use in wet locations









 A	В	C
81/2"	81/2"	81/2"
216 mm	216 mm	216 mm

ORDERING INFORMATION

Catalog Number	Wattage/Voltage	Finish	Start Temperature	Weight Ibs. (kg)
High Pressure Sodium - Polycarbonate Lens				
WPH-70S	70 HPS 120V	Bronze	-40°F	8 (3.6)
WPH-100S	100 HPS 120V	Bronze	-40°F	9 (4.1)
Pulse Start Metal Halide - Glass Refractor				
WGH-70H	70 PSMH 120/208/240/277V	Bronze	-20°F	9 (4.1)
WGH-100H	100 PSMH 120/208/240/277V	Bronze	-20°F	10 (4.5)

ACCESSORIES - Order Separately

Catalog Number	Description
PBT-1	Photocontrol, 120V
PBT-234	Photocontrol, 208, 240, 277V

REPLACEMENT PARTS

Catalog Number	Description	
SM704-REPLGL	Glass only for WGH	
SM704-FRAME/GLASS	Lens door assembly for WGH	
SM705-LENS	Polycarbonate refractor only for WPH	
SM704-SHIELD	Polycarbonate shield for glass WGH	
SM704-GUARD	Wire guard for glass WGH	

PHOTOMETRIC REPORTS

Catalog Number	Report #
WPH-100S	HP08271.IES
WGH-100H	HP08272.IES

Due to our continued efforts to improve our products, product specifications are subject to change without notice.



Hubbell Outdoor Lighting ● 701 Millennium Boulevard ● Greenville, SC 29607 ● PHONE: 864-678-1000 For more information visit our web site: **www.hubbelloutdoor.com**