

BreathAudio Pulse BA-200 Specifications

Number of Channels	2
Power Output	70 Watts at 8 Ohms 100 Watts at 4 ohms
Rated THD	0.80%
Frequency Response at 1 watt ±1 dB	20Hz to 20 kHz
Input Impedance	22 kohms
Voltage Trigger AC or DC	3 to 30 Volts
Unit ON/OFF	+12 Volts DC 75 mA
AC Power	120 VAC, 60Hz 250Watts

Power Consumption	Off, 6.8 watts
4 ohms 1 kHz	On, no signal 7.6 Watts 1/10 power, 29.2 Watts 1/3 power, 79.9 Watts Full power, 405 Watts
Line Fuse Rating	4 amp time lag
Dimensions	8.5 in W x 3.75 in H x 13.5 in L 214 mm W x 96 mm H x 340 mm L
Weight (unit)	12 lbs (4.54 kg)
Weight (shipping)	17.2 lbs (6.51 kg)